

# HAFFMANS c-TPO INPACK TPO/CO<sub>2</sub> METER

PRODUCT LEAFLET



## GENERAL PRODUCT INFORMATION

In the beer and beverage industries both oxygen (O<sub>2</sub>) and carbon dioxide (CO<sub>2</sub>) are important gases. When it comes to product life and flavor stability, oxygen is detrimental. Preventing O<sub>2</sub> pick-ups during the entire production and packaging process is of paramount importance. As a result, beer and beverages are produced with very low dissolved oxygen (DO) levels, to achieve consistent quality and high flavor stability during the product's shelf life. The content of dissolved CO<sub>2</sub> is decisive to the quality and taste of beer and carbonated beverages. Therefore, brewers and beverage manufacturers continuously control and measure the CO<sub>2</sub> content in bottled and canned beverages.

The automatic Inpack TPO/CO<sub>2</sub> Meter, type c-TPO meets the demands. The differentiated measurement of headspace O<sub>2</sub> and DO provides immediate insight in the performance of the filling operation. The multiple routine determinations of TPO and CO<sub>2</sub> are fully automated. Up to 100 different product types/packages can be programmed and easily selected. The instrument is suited for the most common sizes of bottles and cans.

Beyond traditional TPO measurement methods and instruments, the c-TPO measures the headspace O<sub>2</sub> and DO by the filler, while at the same time the liquid remains in the package and is not consumed by the instrument. Sample preparation time is skipped and lab space is minimized. The c-TPO also supports the well-known z-factor method according to Uhlig. The CO<sub>2</sub> content is measured according to Henry's Law.

## BENEFITS

- High quality beer and beverages in every package
  - prevent inferior product entering the market
  - save time and money and maximize the ROI
  - no sample preparation
  - fully automated measurement
- All-in-one measurement: HSO, DO, TPO and CO<sub>2</sub>
  - reduce process downtime
  - prevent product losses
  - low maintenance

## APPLICATIONS

- Laboratory, applicable in breweries and soft drink industries
- Filling department, applicable in breweries and soft drink industries

# HAFFMANS c-TPO INPACK TPO/CO<sub>2</sub> METER

PRODUCT LEAFLET



## TECHNICAL DATA

### Measuring range

TPO, HSO, DO, Headspace Volume, CO<sub>2</sub>,  
Temperature, Pressure

### Measuring range

Oxygen content	0.00 - 4.18%
DO value	0.000 - 2.000 mg/l
CO <sub>2</sub> value	2.0 - 15.0 g/l
HS volume	0.0 - 500 ml
Temperature	-5.0 - 40.0 °C
Pressure	0.00 - 5.00 barg

### Accuracy

DO value	± (1 ppb + 2% m.v.)*
CO <sub>2</sub> value	± 0.1 g/l
Temperature	± 0.2 °C
Pressure	± 0.02 bar

### Memory capacity

Up to 250 measurements

### Bottle dimensions

Height min.	90 mm - max. 440 mm
Diameter min.	55 mm - max. 200 mm

### Can dimensions

Height min.	80 mm - max. 195 mm
Diameter min.	50 mm - max. 73 mm

### Voltage

80-240 V / AC 50-60 Hz

### Interface

USB, barcode reader

### Dimensions

max.	550 x 330 x 1120 (LxWxH mm)
min.	550 x 330 x 680 (LxWxH mm)

### Weight

40 kg

\* at 20 °C

## SCOPE OF SUPPLY

- Inpack TPO/CO<sub>2</sub> Meter, type c-TPO
- Mains cable (Euro, US, UK or AUS plug)
- Service set with piercers and sealing rubbers
- Software set (CD + Interface cable)
- Instruction manual

## OPTIONS

- Certificate of measurement
- PET bottle holder
- Barcode reader



HAFFMANS BV

P.O. BOX 3150 NL-5902 RD VENLO, NETHERLANDS WWW.HAFFMANS.NL

All Pentair trademarks and logos are owned by Pentair, Inc. All other brand or product names are trademarks or registered marks of their respective owners. Because we are continuously improving our products and services, Pentair reserves the right to change specifications without prior notice.

Pentair is an equal opportunity employer.

c-TPO E-4 /12 © 2012 Pentair, Inc. All Rights Reserved.

